

Floating Wand Basin Square



Scan QR code
to view our
installation notes



To order this item please advise:


- If optional Tempering Valve required

HBFWs



Product Info:

- User activates spout by leaning against wand
- Complies with food handling standards
- No electrical or power requirements
- Supplied pre-plumbed including PLV
- 45° chamfered front corners
- 40mm waste and wall bracket supplied
- Supplied with gooseneck spout
- Optional tempering valve



INSTALLATION NOTES

1) Fixture strength is ultimately determined by the load capacity of the supporting structure (noggins recommended for stud walls) and use of appropriate fixings. 2) Basin is secured to wall with an offset bracket positioned behind the splashback and via 8mm fixing holes integrated into tags at the back of the basin body. 3) Minimum flow pressure to 1/2" PLV connection = 200kPa. 4) Tempering valve supplied only by request. Suggested mounting height 850-900mm FFL to basin rim.

